

Kellems Wire Pulling Grips, Underground Rotating Eye, 2.00- 2.49 in, Standard

By Hubbell Wiring Device-Kellems

Catalog # [03301027](#)

Kellems Wire Management, Pulling Grips, Underground Rotating
Eye, 2.00-2.49", Standard



General

Application	Underground Pulling
Approx Breaking Strength	27,200 lbs
Catalog Number	03301027
Color	
Construction	Woven
EU RoHS Indicator	Yes
Load Capacity	5440
Material	Steel, Galvanized
Material - Mounting Hardware	Non-Mounted
Performance	Mechanical - Approximate Breaking Strength - 27,200 (120,986) Lbs. (N) Mechanical - Cable Diameter Range - 2.00"-2.49" (5.08-6.32) Mechanical - Working Load - 5440 (24197.2) Lbs. (N)
Series	Underground K-Type
Style	Closed Mesh, Double Weave
Type	Rotating Eye, Standard Length
UPC	783585314310
Working Load Limit	5,440 lb

Dimensions

Weight	4.1 lb
--------	--------

Conductor Related

Cable Diameter Range	2.00 in - 2.49 in
Cable Diameter Range Metric	5.08 cm - 6.32 cm
Cable Size	2.00"-2.49" (5.08-6.32)
Cable Specification	UL Listed Circuit Wire

Certifications And Compliance

Industry Standard(s)	CSA Certified
----------------------	---------------

Logistics

Carton Quantity	2
-----------------	---

Product Assets

[Catalogs - WDK Catalog Full 2024](#)

[Literature - Wire Management Solutions Brochure](#)

[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-03301027-SPEC-EN | REV 6/2024