

Kellems Wire Management, Pulling Grips, Overhead Rotating Eye, 1.00-1.24"

By Hubbell Wiring Device-Kellems
Catalog # [03302022](#)

Kellems Wire Management, Pulling Grips, Overhead Rotating Eye, 1.00-1.24"



Application

Overhead Pulling

Performance

- Mechanical - Approximate Breaking Strength - 24,600 (109,420) Lbs. (N)
- Mechanical - Cable Diameter Range - 1.00"-1.24" (2.54-3.15)
- Mechanical - Working Load - 4920 (21884) Lbs. (N)

General

Approx Breaking Strength	24,600 lbs
Catalog Number	03302022
Color Code	Gold
Construction	Woven
EU RoHS Indicator	Yes
Load Capacity	4920
Material	Steel, Galvanized
Material - Mounting Hardware	Non-Mounted
Series	Overhead Multiple Strength
Specifications	<ul style="list-style-type: none">• Eye - Steel• Shoulders - Aluminum• Strand - Galvanized Steel

Style	• Tag - Mylar Closed Mesh, Triple, Double, Single Weave
Type	Rotating Eye
UPC	783585314518

Conductor Related

Cable Diameter Range	1.00 in-1.24 in
Cable Size	1.00"-1.24" (2.54-3.15)
Cable Specification	UL Listed Circuit Wire

Certifications And Compliance

Industry Standard(s)	CSA Certified
----------------------	---------------

Logistics

Carton Quantity	2
-----------------	---

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Specifications - 3302022](#)
- [Warranty - Industrial & Commercial Products](#)