

## Kellems Wire Pulling Grips, Overhead Flexible Eye, .75-.99 in

By Hubbell Wiring Device-Kellems

Catalog # 03302048

Kellems Wire Management, Pulling Grips, Overhead Flexible Eye,  
.75-.99"



### Application

Overhead Pulling

### Performance

- Mechanical - Approximate Breaking Strength - 14,400 (64,051) Lbs. (N)
- Mechanical - Cable Diameter Range - .75"--.99" (1.90-2.51)
- Mechanical - Working Load - 2880 (12810.2) Lbs. (N)

### General

Approx Breaking Strength	14,400 lbs
Catalog Number	03302048
Color Code	Light Blue
Construction	Woven
EU RoHS Indicator	Yes
Load Capacity	2880
Material	Steel, Galvanized
Material - Mounting Hardware	Non-Mounted
Series	Overhead Multiple Strength
Specifications	<ul style="list-style-type: none"><li>• Eye - Galvanized steel</li><li>• Lug - Aluminum</li><li>• Shoulders - Aluminum</li><li>• Strand - Galvanized Steel</li><li>• Tag - Mylar</li></ul>
Style	Closed Mesh, Triple, Double, Single Weave

Type	Flexible Eye
UPC	783585314587
Working Load Limit	2,880 lb

### Dimensions

Weight	1.4 lb
--------	--------

### Conductor Related

Cable Diameter Range	0.75 in-0.99 in
Cable Diameter Range Metric	1.90 cm - 2.51 cm
Cable Size	.75"--.99" (1.90-2.51)
Cable Specification	UL Listed Circuit Wire

### Certifications And Compliance

Industry Standard(s)	CSA Certified
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	5
-----------------	---

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Literature - Wire Management Solutions Brochure](#)  
[Specifications - 3302048](#)  
[Warranty - Industrial & Commercial Products](#)