

Kellems Wire Management, Pulling Grips, Light Duty Flexible Eye, .63-.74", Standard

By Hubbell Wiring Device-Kellems
Catalog # [03303011](#)

Kellems Wire Management, Pulling Grips, Light Duty Flexible Eye,.63-.74", Standard



Application

General Cable Pulling

Performance

- Mechanical - Approximate Breaking Strength - 2,800 (12,454) Lbs. (N)
- Mechanical - Working Load - 560 (2490.8) Lbs. (N)

General

Approx Breaking Strength	2,800 lbs
Catalog Number	03303011
Construction	Woven
EU RoHS Indicator	Yes
Load Capacity	560
Material	Steel, Galvanized
Material - Mounting Hardware	Non-Mounted
Series	Light Duty Grip
Specifications	<ul style="list-style-type: none">• Lug - Aluminum• Shoulders - Aluminum• Strand - Galvanized steel

Style
Type
UPC

- Tag - Mylar
- Closed Mesh, Single Weave
Flexible Eye, Standard Length
783585314846

Conductor Related

Cable Diameter Range	0.63 in-0.74 in
Cable Size	.63"-.74" (1.60-1.88)
Cable Specification	UL Listed Circuit Wire

Certifications And Compliance

Industry Standard(s)	CSA Certified
Standards - RoHS Compliance Status	CM

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Specifications - 3303011](#)
- [Warranty - Industrial & Commercial Products](#)