

Kellems Wire Management, Pulling Grips, Light Duty Flexible Eye, .75-.99", Standard

By Hubbell Wiring Device-Kellems
Catalog # [03303012](#)

Kellems Wire Management, Pulling Grips, Light Duty Flexible Eye,.75-.99", Standard



Application

General Cable Pulling

Performance

- Mechanical - Approximate Breaking Strength - 4,000 (17,792) Lbs. (N)
- Mechanical - Working Load - 800 (3558.4) Lbs. (N)

General

Approx Breaking Strength	4,000 lbs
Catalog Number	03303012
Construction	Woven
EU RoHS Indicator	Yes
Load Capacity	800
Material	Steel, Galvanized
Material - Mounting Hardware	Non-Mounted
Series	Light Duty Grip
Specifications	<ul style="list-style-type: none">• Lug - Aluminum• Shoulders - Aluminum• Strand - Galvanized steel• Tag - Mylar
Style	Closed Mesh, Single Weave

Type
UPC

Flexible Eye, Standard Length
783585314853

Conductor Related

Cable Diameter Range	0.75 in-0.99 in
Cable Size	.75"- .99" (1.90-2.51)
Cable Specification	UL Listed Circuit Wire

Certifications And Compliance

Industry Standard(s)	CSA Certified
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Specifications - 3303012](#)
- [Warranty - Industrial & Commercial Products](#)