

Kellems Wire Management, Slack Pulling Grips, Single Offset Eye, .75-.99"

By Hubbell Wiring Device-Kellems
Catalog # [03308003](#)

Kellems Wire Management, Slack Pulling Grips, Single Offset Eye, .75-.99"



Application

General Cable Pulling

Performance

- Mechanical - Approximate Breaking Strength - 2,600 (11,565) Lbs. (N)
- Mechanical - Working Load - 520 (2313) Lbs. (N)

General

Approx Breaking Strength	2,600 lbs
Catalog Number	03308003
Construction	Woven
EU RoHS Indicator	Yes
Load Capacity	520
Material	Steel, Galvanized
Material - Mounting Hardware	Non-Mounted
Series	Slack Grip
Specifications	<ul style="list-style-type: none">• Lug - Aluminum• Strand - Galvanized steel• Tab - Copper• Tag - Mylar

Style
Type
UPC

Closed Mesh, Double Weave
Offset Eye
783585316222

Conductor Related

Cable Diameter Range	0.75 in-0.99 in
Cable Size	.75"- .99" (1.90-2.51)
Cable Specification	UL Listed Circuit Wire

Certifications And Compliance

Industry Standard(s)	CSA Certified
----------------------	---------------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Specifications - 3308003](#)
- [Warranty - Industrial & Commercial Products](#)