

Kellems Wire Management, Slack Pulling Grips, Single Offset Eye, 1.25-1.49"

By Hubbell Wiring Device-Kellems
Catalog # [03308005](#)

Kellems Wire Management, Slack Pulling Grips, Single Offset Eye, 1.25-1.49"



Application

General Cable Pulling

Performance

- Mechanical - Approximate Breaking Strength - 5,400 (24,019) Lbs. (N)
- Mechanical - Working Load - 1080 (4803.8) Lbs. (N)

General

Approx Breaking Strength	5,400 lbs
Catalog Number	03308005
Construction	Woven
EU RoHS Indicator	Yes
Load Capacity	1080
Material	Steel, Galvanized
Material - Mounting Hardware	Non-Mounted
Series	Slack Grip
Specifications	<ul style="list-style-type: none">• Lug - Aluminum• Strand - Galvanized steel• Tab - Copper• Tag - Mylar
Style	Closed Mesh, Double Weave

Type
UPC

Offset Eye
783585316246

Conductor Related

Cable Diameter Range	1.25 in-1.49 in
Cable Size	1.25"-1.49" (3.17-3.78)
Cable Specification	UL Listed Circuit Wire

Certifications And Compliance

Industry Standard(s)	CSA Certified
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	2
-----------------	---

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Specifications - 3308005](#)
- [Warranty - Industrial & Commercial Products](#)