

Kellems Wire Management, Slack Pulling Grips, Rawhide Lace Closing, Offset Eye, 2.00-2.49", Standard

By Hubbell Wiring Device-Kellems
Catalog # [03309008](#)

Kellems Wire Management, Slack Pulling Grips, Rawhide Lace Closing, Offset Eye, 2.00-2.49", Standard



Application

General Cable Pulling

Performance

- Mechanical - Approximate Breaking Strength - 4,000 (17,792) Lbs. (N)
- Mechanical - Working Load - 800 (3558.4) Lbs. (N)

General

Approx Breaking Strength	4,000 lbs
Catalog Number	03309008
Construction	Woven
EU RoHS Indicator	Yes
Load Capacity	800
Material	Steel, Galvanized
Material - Mounting Hardware	Non-Mounted
Series	Slack Grip
Specifications	<ul style="list-style-type: none">• Lace - Rawhide• Lug - Aluminum• Strand - Galvanized steel• Tab - Copper• Tag - Mylar

Style

Split Mesh, Rawhide Lace Closing, Double Weave

Type

Offset Eye

UPC

783585316499

Conductor Related

Cable Diameter Range

2.00 in-2.49 in

Cable Size

2.00"-2.49" (5.08-6.32)

Cable Specification

UL Listed Circuit Wire

Certifications And Compliance

Industry Standard(s)

CSA Certified

Logistics

Carton Quantity

2

Product Assets

[Catalogs - WDK Catalog Full 2024](#)

[Literature - Wire Management Solutions Brochure](#)

[Specifications - 3309008](#)

[Warranty - Industrial & Commercial Products](#)