

Kellems Wire Management, Dusttight Grips, Strain Relief, .24-.32", 1/2" Non-Insulated

By Hubbell Wiring Device-Kellems
Catalog # [073031200](#)



Kellems Wire Management, Dusttight Grips, Strain Relief,
.24-.32", 1/2" Non-Insulated

Application

Light Duty

Performance

- Environmental - Flammability - UL 94HB (Strand grip), UL 94V-2 (Fitting)
- Environmental - Hazardous Locations - Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C

General

Catalog Number	073031200
Construction	Woven
EU RoHS Indicator	Yes
Item Type	Dust-Tight Strain Relief Grips
Material	Aluminum Fittings, Galvanized Steel Mesh
Material - Mounting Hardware	Locknut or Tapped Hole
Series	Dust-Tight
Specifications	<ul style="list-style-type: none">• Body - Aluminum• Locknut - Steel• Sleeve - Aluminum• Strand - Galvanized Steel
Style	For Insulated Cables

Thread Size	1/2" NPT
Type	Non-Insulated, Wide Range
UPC	783585330006

Dimensions

Display Size	1/2" NPT
Trade Size	0.5

Conductor Related

Cable Diameter Range	0.24 in-0.32 in
Cable Size	.24"- .32" (.61-.81)

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Specifications - 73031200](#)
- [Warranty - Industrial & Commercial Products](#)