

Kellems Wire Management, Dusttight Grips, Strain Relief, .97- 1.25", 1 1/4", Non-Insulated

By Hubbell Wiring Device-Kellems
Catalog # [073031205](#)



Kellems Wire Management, Dusttight Grips, Strain Relief, .97-
1.25", 1 1/4", Non-Insulated

Application

- Light Duty

Performance

- Environmental - Flammability - UL 94HB (Strand grip), UL 94V-2 (Fitting)
- Environmental - Hazardous Locations - Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C

General

Catalog Number	073031205
Construction	Woven
EU RoHS Indicator	Yes
Item Type	Dust-Tight Strain Relief Grips
Material	Aluminum Fittings, Galvanized Steel Mesh
Material - Mounting Hardware	Locknut or Tapped Hole
Series	Dust-Tight
Specifications	<ul style="list-style-type: none">• Body - Aluminum• Locknut - Steel• Sleeve - Aluminum• Strand - Galvanized Steel
Style	For Insulated Cables
Thread Size	1 1/4" NPT

Type	Non-Insulated, Wide Range
UPC	783585330051

Dimensions

Display Size	1 1/4" NPT
Trade Size	1.25

Conductor Related

Cable Diameter Range	0.97 in-1.25 in
Cable Size	.97"-1.25" (2.46-3.17)

Certifications And Compliance

Industry Standard(s)	UL Listed
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
Pallet Quantity	1200

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - Wire Management Solutions Brochure](#)
[Specifications - 73031205](#)
[Warranty - Industrial & Commercial Products](#)