

Kellems Wire Management, Dusttight Grips, Strain Relief, .43-.54", 1/2", Insulated

By Hubbell Wiring Device-Kellems

Catalog # [073031208](#)

Kellems Wire Management, Dusttight Grips, Strain Relief,
.43-.54", 1/2", Insulated



General

Application	Light Duty
Approx Breaking Strength	650 lbs
Catalog Number	073031208
Color	
Construction	Woven
EU RoHS Indicator	Yes
Item Type	Dust-Tight Strain Relief Grips
Material	Aluminum Fittings, Galvanized Steel Mesh
Material - Mounting Hardware	Locknut or Tapped Hole
Performance	Environmental - Flammability - UL 94HB (Strand grip), UL 94V-2 (Fitting) Environmental - Hazardous Locations - Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C
Series	Dust-Tight
Style	For Insulated Cables
Thread Size	1/2" NPS
Type	Insulated, Wide Range
UPC	783585330082

Dimensions

Dimension - Thread Size	1" (2.54)
Display Size	Standard Sized
Trade Size	0.5

Conductor Related

Cable Diameter Range	0.43 in-0.54 in
Cable Size	.43"-.54" (1.09-1.37)
Cable Specification	Mesh Length @ Nom. Dia. : 4.75" (12.06 cm)

Certifications And Compliance

Industry Standard(s)	UL Listed
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	20
Pallet Quantity	6480

Product Assets

[Catalogs - WDK Catalog Full 2024](#)

[Literature - Wire Management Solutions Brochure](#)

[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-073031208-SPEC-EN | REV 6/2024