

Kellems Wire Management, Dusttight Grips, Strain Relief, .97- 1.25", 1.25", Insulated

By Hubbell Wiring Device-Kellems

Catalog # [073031211](#)

Kellems Wire Management, Dusttight Grips, Strain Relief, .97-
1.25", 1.25", Insulated



General

Application	Light Duty
Approx Breaking Strength	1,200 lbs
Catalog Number	073031211
Color	
Construction	Woven
EU RoHS Indicator	Yes
Item Type	Dust-Tight Strain Relief Grips
Material	Aluminum Fittings, Galvanized Steel Mesh
Material - Mounting Hardware	Locknut or Tapped Hole
Performance	Environmental - Flammability - UL 94HB (Strand grip), UL 94V-2 (Fitting)
	Environmental - Hazardous Locations - Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C
Series	Dust-Tight
Style	For Insulated Cables
Thread Size	1 1/4" NPS
Type	Insulated, Wide Range
UPC	783585330112

Dimensions

Dimension - Thread Size	1.313" (3.02)
Display Size	Standard Sized
Trade Size	1.25

Conductor Related

Cable Diameter Range	0.97 in-1.25 in
Cable Size	.97"-1.25" (2.46-3.17)
Cable Specification	Mesh Length @ Nom. Dia. : 9" (22.86 cm)

Certifications And Compliance

Industry Standard(s)	UL Listed
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
Pallet Quantity	1080

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-073031211-SPEC-EN | REV 6/2024