

Kellems Wire Management, Dusttight Grips, Strain Relief, 1.50- 1.70", 2", Insulated

By Hubbell Wiring Device-Kellems
Catalog # [073031213](#)



Kellems Wire Management, Dusttight Grips, Strain Relief, 1.5-1.7",
2", Insulated

Application

- Light Duty

Performance

- Environmental - Flammability - UL 94HB (Strand grip), UL 94V-2 (Fitting)
- Environmental - Hazardous Locations - Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C

General

Approx Breaking Strength	3,000 lbs
Catalog Number	073031213
Construction	Woven
EU RoHS Indicator	Yes
Item Type	Dust-Tight Strain Relief Grips
Material	Aluminum Fittings, Galvanized Steel Mesh
Material - Mounting Hardware	Locknut or Tapped Hole
Series	Dust-Tight
Specifications	<ul style="list-style-type: none">• Body - Aluminum• Bushing - Plastic• Locknut - Steel• Seal - Neoprene• Sleeve - Aluminum• Strand - Galvanized Steel
Style	For Insulated Cables

Thread Size	2" NPT
Type	Insulated, Wide Range
UPC	783585330136

Dimensions

Dimension - Thread Size	1.375" (3.49)
Display Size	Standard Sized
Trade Size	2

Conductor Related

Cable Diameter Range	1.50 in-1.70 in
Cable Size	1.50"-1.70" (3.81-4.32)
Cable Specification	Mesh Length @ Nom. Dia. : 13.25" (33.65 cm)

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	15
Pallet Quantity	825

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - Wire Management Solutions Brochure](#)
[Specifications - 73031213](#)
[Warranty - Industrial & Commercial Products](#)