

## Kellems Wire Management, I-Grips, .73-.85", Galvanized

By Hubbell Wiring Device-Kellems  
Catalog # [07310004](#)

Kellems Wire Management, I-Grips, .73-.85", Galvanized



### Application

Light Duty

### General

Approx Breaking Strength	250 lbs
Catalog Number	07310004
Construction	Woven
EU RoHS Indicator	Yes
Item Type	I-Grips
Material	Galvanized Steel Mesh for Insulated Cables, Plastic Coated
Material - Mounting Hardware	Mounts on Cord Grip For Plug & Connectors
Series	For Plug & Connectors
Specifications	<ul style="list-style-type: none"><li>• Eye - Aluminum</li><li>• Strand - Galvanized Steel</li><li>• Tube - Plastic</li></ul>
Style	I-Grips, For Hubbell Devices
Type	Eyelets (2)
UPC	783585332178

### Dimensions

Display Size

Standard Sized

### Conductor Related

Cable Diameter Range	0.73 in-0.85 in
Cable Size	.73"-.85" (1.85-2.16)
Cable Specification	Mesh Length @ Nom. Dia. : 6.5" (16.51 cm)

### Certifications And Compliance

Industry Standard(s)	UL Listed
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	20
Pallet Quantity	6480

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Literature - Wire Management Solutions Brochure](#)  
[Specifications - 7310004](#)  
[Warranty - Industrial & Commercial Products](#)