



Kellems Wire Management, Deluxe Cord Grips, Straight Male, .312-.375", 3/8" with Mesh

By Hubbell Wiring Device-Kellems
Catalog # [07401002](#)

Kellems Wire Management, Deluxe Cord Grips, Straight Male, .312-.375", 3/8" with Mesh



Application

Straight Male- Form 1

General

Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Sealing Ring Between Box And Fitting.
Item Type	Deluxe Cord Grips
Material	Aluminum Fittings, Stainless Steel Mesh
Material - Mounting Hardware	Locknut or Tapped Opening
Performance	<ul style="list-style-type: none"> • Environmental - Flammability - UL 94HB (Strand grip), UL 94V-2(Fitting) • Environmental - Hazardous Locations - Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C • Environmental - Operating Temperatures - -30°F to +240°F (-34°C to +115°C) • Environmental - Wet Locations - Suitable for use in wet locations when used with a listed sealing ring between box and fitting
Series	Deluxe Cord Grips
Style	For Insulated Cables
Temperature Rating	Minimum -30 Deg F to 240 Deg F (-34 Deg C to 115 Deg C)
Thread Size	3/8" NPT
Type	<ul style="list-style-type: none"> • Straight Male Thread • Straight Male Thread
UPC	783585321820

Dimensions

Display Size 3/8" NPT

Conductor Related

Cable Diameter Range	0.312 in-0.375 in
Cable Size	.312"-.375" (.79-.95)
Conductor Range	0.312-0.375 in (.79-.95 mm)
Number Of Conductors	Single

Certifications and Compliance

Industry Standard(s)	UL Listed
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity 5

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Literature - Wire Management Solutions Brochure](#)
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

