

# Kellems Wire Management, Deluxe Cord Grips, Straight Male, .187-.250", 1/2" with Mesh

By Hubbell Wiring Device-Kellems

Catalog # [07401004](#)

Kellems Wire Management, Deluxe Cord Grips, Straight Male,  
.187-.250", 1/2" with Mesh



## General

Application	Straight Male- Form 2
Catalog Number	07401004
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Sealing Ring Between Box And Fitting.
Item Type	Deluxe Cord Grips
Material	Aluminum Fittings, Stainless Steel Mesh
Material - Mounting Hardware	Locknut or Tapped Opening
Performance	Environmental - Flammability - UL 94HB (Strand grip), UL 94V-2(Fitting)  Environmental - Hazardous Locations - Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C  Environmental - Operating Temperatures - -30°F to +240°F (-34°C to +115°C)  Environmental - Wet Locations - Suitable for use in wet locations when used with a listed sealing ring between box and fitting
Series	Deluxe Cord Grips
Style	For Insulated Cables
Temperature Rating	Minimum -30 Deg F to 240 Deg F (-34 Deg C to 115 Deg C)
Thread Size	1/2" NPT
Type	Straight Male Thread
UPC	783585321844

## Dimensions

Display Size	1/2" NPT
--------------	----------

## Conductor Related

Cable Diameter Range	0.187 in-0.250 in
Cable Size	.187"-.250" (.47-.63)
Conductor Range	0.187-0.25 in (.47-.63 mm)
Number of Conductors	Single

## Certifications And Compliance

Industry Standard(s)	UL Listed
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	5
Pallet Quantity	1620

## Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Literature - Multi-Hole Cord Grip Connectors](#)
- [Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-07401004-SPEC-EN | REV 6/2024