

Kellems Wire Management, Deluxe Cord Grips, Straight Male, .250-.375", 1/2" with Mesh

By Hubbell Wiring Device-Kellems

Catalog # [07401006](#)

Kellems Wire Management, Deluxe Cord Grips, Straight Male,
.250-.375", 1/2" with Mesh



General

Application	Straight Male- Form 2
Catalog Number	07401006
Color	
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Sealing Ring Between Box And Fitting.
Item Type	Deluxe Cord Grips
Material	Aluminum Fittings, Stainless Steel Mesh
Material - Mounting Hardware	Locknut or Tapped Opening
Performance	Environmental - Flammability - UL 94HB (Strand grip), UL 94V-2(Fitting) Environmental - Hazardous Locations - Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C Environmental - Operating Temperatures - -30°F to +240°F (-34°C to +115°C) Environmental - Wet Locations - Suitable for use in wet locations when used with a listed sealing ring between box and fitting
Series	Deluxe Cord Grips
Style	For Insulated Cables
Temperature Rating	Minimum -30 Deg F to 240 Deg F (-34 Deg C to 115 Deg C)
Thread Size	1/2" NPT
Type	Straight Male Thread
UPC	783585321868

Dimensions

Display Size	1/2" NPT
--------------	----------

Conductor Related

Cable Diameter Range	0.250 in-0.375 in
Cable Size	.250"-.375" (.63-.95)
Conductor Range	0.25-0.375 in (.63-.95 mm)
Number of Conductors	Single

Certifications And Compliance

Industry Standard(s)	UL Listed
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	5
Pallet Quantity	1620

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-07401006-SPEC-EN | REV 6/2024