

Kellems Wire Management, Deluxe  
Cord Grips, Straight Male,  
.250-.375", 1/2" with Mesh

By Hubbell Wiring Device-Kellems  
Catalog # 07401006

Kellems Wire Management, Deluxe Cord Grips, Straight Male,  
.250-.375", 1/2" with Mesh

Application

Straight Male- Form 2

Performance

- Environmental - Flammability - UL 94HB (Strand grip), UL 94V-2(Fitting)
- Environmental - Hazardous Locations - Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C
- Environmental - Operating Temperatures - -30°F to +240°F (-34°C to +115°C)
- Environmental - Wet Locations - Suitable for use in wet locations when used with a listed sealing ring between box and fitting

General

Catalog Number	07401006
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Sealing Ring Between Box And Fitting.
Item Type	Deluxe Cord Grips
Material	Aluminum Fittings, Stainless Steel Mesh
Material - Mounting Hardware Series	Locknut or Tapped Opening Deluxe Cord Grips
Specifications	<ul style="list-style-type: none"><li>Body - Aluminum</li><li>Bushing - Neoprene</li><li>Nut - Aluminum</li><li>Strand - Stainless Steel</li></ul>



Style	For Insulated Cables
Temperature Rating	Minimum -30 Deg F to 240 Deg F (-34 Deg C to 115 Deg C)
Thread Size	1/2" NPT
Type	Straight Male Thread
UPC	783585321868

Dimensions

Display Size	1/2" NPT
--------------	----------

Conductor Related

Cable Diameter Range	0.250 in-0.375 in
Cable Size	.250"-.375" (.63-.95)
Conductor Range	0.25-0.375 in (.63-.95 mm)
Number of Conductors	Single

Certifications And Compliance

Industry Standard(s)	UL Listed
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	5
Pallet Quantity	1620

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Specifications - 7401006](#)
- [Warranty - Industrial & Commercial Products](#)