

# Kellems Wire Management, Deluxe Cord Grips, Straight Male, .375-.500", 1/2" with Mesh

By Hubbell Wiring Device-Kellems  
Catalog # [07401008](#)



Kellems Wire Management, Deluxe Cord Grips, Straight Male, .375-.500", 1/2" with Mesh

## Application

- Straight Male- Form 2

## Performance

- Environmental - Flammability - UL 94HB (Strand grip), UL 94V-2(Fitting)
- Environmental - Hazardous Locations - Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C
- Environmental - Operating Temperatures - -30°F to +240°F (-34°C to +115°C)
- Environmental - Wet Locations - Suitable for use in wet locations when used with a listed sealing ring between box and fitting

## General

Catalog Number	07401008
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Sealing Ring Between Box And Fitting.
Item Type	Deluxe Cord Grips
Material	Aluminum Fittings, Stainless Steel Mesh
Material - Mounting Hardware Series	Locknut or Tapped Opening Deluxe Cord Grips
Specifications	<ul style="list-style-type: none"><li>• Body - Aluminum</li><li>• Bushing - Neoprene</li><li>• Nut - Aluminum</li><li>• Strand - Stainless Steel</li></ul>

Style	For Insulated Cables
Temperature Rating	Minimum -30 Deg F to 240 Deg F (-34 Deg C to 115 Deg C)
Thread Size	1/2" NPT
Type	Straight Male Thread
UPC	783585321899

## Dimensions

Display Size	1/2" NPT
--------------	----------

## Conductor Related

Cable Diameter Range	0.375 in-0.500 in
Cable Size	.375"-.500" (.95-1.27)
Conductor Range	0.375-0.5 in (.95-1.27 mm)
Number of Conductors	Single

## Certifications And Compliance

Industry Standard(s)	UL Listed
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	5
Pallet Quantity	1620

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Literature - Wire Management Solutions Brochure](#)  
[Literature - Multi-Hole Cord Grip Connectors](#)  
[Specifications - 7401008](#)  
[Warranty - Industrial & Commercial Products](#)