

# Kellems Wire Management, Deluxe Cord Grips, Straight Male, .500-.625", 3/4" with Mesh

By Hubbell Wiring Device-Kellems  
Catalog # 07401017

Kellems Wire Management, Deluxe Cord Grips, Straight Male, .500-.625", 3/4" with Mesh



## Application

Straight Male- Form 2

## Performance

- Environmental - Flammability - UL 94HB (Strand grip), UL 94V-2(Fitting)
- Environmental - Hazardous Locations - Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C
- Environmental - Operating Temperatures - -30°F to +240°F (-34°C to +115°C)
- Environmental - Wet Locations - Suitable for use in wet locations when used with a listed sealing ring between box and fitting

## General

|                                     |  |
|-------------------------------------|--|
| Catalog Number                      | 07401017   |
| EU RoHS Indicator                   | Yes  |
| Environmental Conditions            | Suitable For Use In Wet Locations When Used With A Listed Sealing Ring Between Box And Fitting.  |
| Item Type                           | Deluxe Cord Grips  |
| Material                            | Aluminum Fittings, Stainless Steel Mesh  |
| Material - Mounting Hardware Series | Locknut or Tapped Opening Deluxe Cord Grips  |
| Specifications                      | <ul style="list-style-type: none"><li>• Body - Aluminum</li><li>• Bushing - Neoprene</li><li>• Nut - Aluminum</li><li>• Strand - Stainless Steel</li></ul> |

|                    |   |
|--------------------|---|
| Style              | For Insulated Cables                                    |
| Temperature Rating | Minimum -30 Deg F to 240 Deg F (-34 Deg C to 115 Deg C) |
| Thread Size        | 3/4" NPT  |
| Type               | Straight Male Thread                                    |
| UPC                | 783585321981  |

## Dimensions

|              |          |
|--------------|----------|
| Display Size | 3/4" NPT |
|--------------|----------|

## Conductor Related

|                      |                             |
|----------------------|-----------------------------|
| Cable Diameter Range | 0.500 in-0.625 in           |
| Cable Size           | .500"-.625" (1.27-1.59)     |
| Conductor Range      | 0.5-0.625 in (1.27-1.59 mm) |
| Number of Conductors | Single                      |

## Certifications And Compliance

|                                    |           |
|------------------------------------|-----------|
| Industry Standard(s)               | UL Listed |
| Standards - RoHS Compliance Status | CM        |

## Logistics

|                 |      |
|-----------------|------|
| Carton Quantity | 5    |
| Pallet Quantity | 1620 |

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Literature - Wire Management Solutions Brochure](#)  
[Specifications - 7401017](#)  
[Warranty - Industrial & Commercial Products](#)