

Kellems Wire Management, Deluxe Cord Grips, Straight Male, .500-.625", 1" with Mesh

By Hubbell Wiring Device-Kellems
Catalog # [07401019](#)

Kellems Wire Management, Deluxe Cord Grips, Straight Male, .500-.625", 1" with Mesh



Application

Straight Male- Form 4

Performance

- Environmental - Flammability - UL 94HB (Strand grip), UL 94V-2(Fitting)
- Environmental - Hazardous Locations - Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C
- Environmental - Operating Temperatures - -30°F to +240°F (-34°C to +115°C)
- Environmental - Wet Locations - Suitable for use in wet locations when used with a listed sealing ring between box and fitting

General

Catalog Number	07401019
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Sealing Ring Between Box And Fitting.
Item Type	Deluxe Cord Grips
Material	Aluminum Fittings, Stainless Steel Mesh
Material - Mounting Hardware Series	Locknut or Tapped Opening Deluxe Cord Grips
Specifications	<ul style="list-style-type: none">• Body - Aluminum• Bushing - Neoprene• Nut - Aluminum

Style
Temperature Rating

Thread Size
Type
UPC

• Strand - Stainless Steel
For Insulated Cables
Minimum -30 Deg F to 240 Deg F (-34 Deg C to 115 Deg C)
1" NPT
Straight Male Thread
783585322001

Dimensions

Display Size 1" NPT

Conductor Related

Cable Diameter Range 0.500 in-0.625 in
Cable Size .500"-.625" (1.27-1.59)
Conductor Range 0.5-0.625 in (1.27-1.59 mm)
Number of Conductors Single

Certifications And Compliance

Industry Standard(s) UL Listed

Logistics

Carton Quantity 5
Pallet Quantity 1500

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - Wire Management Solutions Brochure](#)
[Specifications - 7401019](#)
[Warranty - Industrial & Commercial Products](#)