

Kellems Wire Management, Deluxe Cord Grips, Straight Male, .875-1.000", 1", with Mesh

By Hubbell Wiring Device-Kellems
Catalog # [07401025](#)

Kellems Wire Management, Deluxe Cord Grips, Straight Male, .875-1.000", 1", with Mesh



Application

- Straight Male- Form 4

Performance

- Environmental - Flammability - UL 94HB (Strand grip), UL 94V-2(Fitting)
- Environmental - Hazardous Locations - Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C
- Environmental - Operating Temperatures - -30°F to +240°F (-34°C to +115°C)
- Environmental - Wet Locations - Suitable for use in wet locations when used with a listed sealing ring between box and fitting

General

Catalog Number	07401025
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Sealing Ring Between Box And Fitting.
Item Type	Deluxe Cord Grips
Material	Aluminum Fittings, Stainless Steel Mesh
Material - Mounting Hardware	Locknut or Tapped Opening
Operating Temperature	-30°F to +240°F (-34°C to +115°C)
Series	Deluxe Cord Grips
Specifications	<ul style="list-style-type: none">• Body - Aluminum• Bushing - Neoprene• Nut - Aluminum

Style
Temperature Rating

- Strand - Stainless Steel For Insulated Cables
Minimum -30 Deg F to 240 Deg F (-34 Deg C to 115 Deg C)

Thread Size
Type
UPC

1" NPT
Straight Male Thread
783585322063

Dimensions

Display Size
Weight

1" NPT
0.3 lb

Conductor Related

Cable Diameter Range
Cable Size
Conductor Range
Number of Conductors

0.875 in-1.000 in
.875"-1.000" (2.22-2.54)
0.875-1 in (2.22-2.54 mm)
Single

Certifications And Compliance

Industry Standard(s)
Standards - RoHS Compliance
Status

UL Listed
CM

Logistics

Carton Quantity
Pallet Quantity

5
1500

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - Wire Management Solutions Brochure](#)
[Specifications - 7401025](#)
[Warranty - Industrial & Commercial Products](#)