

Kellems Wire Management, Deluxe Cord Grips, Straight Male, 1.687-1.812", 2" with Mesh

By Hubbell Wiring Device-Kellems
Catalog # [07401035](#)

Kellems Wire Management, Deluxe Cord Grips, Straight Male, 1.687-1.812", 2" with Mesh



Application

- Straight Male- Form 6

Performance

- Environmental - Flammability - UL 94HB (Strand grip), UL 94V-2(Fitting)
- Environmental - Hazardous Locations - Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C
- Environmental - Operating Temperatures - -30°F to +240°F (-34°C to +115°C)
- Environmental - Wet Locations - Suitable for use in wet locations when used with a listed sealing ring between box and fitting

General

Catalog Number	07401035
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Sealing Ring Between Box And Fitting.
Item Type	Deluxe Cord Grips
Material	Aluminum Fittings, Stainless Steel Mesh
Material - Mounting Hardware Series	Locknut or Tapped Opening Deluxe Cord Grips
Specifications	<ul style="list-style-type: none">• Body - Aluminum• Bushing - Neoprene

Style

Temperature Rating

Thread Size

Type

UPC

Dimensions

Display Size

Conductor Related

Cable Diameter Range

Cable Size

Conductor Range

Number of Conductors

- Nut - Aluminum

- Strand - Stainless Steel For Insulated Cables

Minimum -30 Deg F to 240 Deg F (-34 Deg C to 115 Deg C)

2" NPT

Straight Male Thread

783585322162

2" NPT

1.687 in- 1.812 in

1.687"-1.812" (4.28-4.60)

1.687-1.812 in (4.28-4.6 mm)

Single

Certifications And Compliance

Industry Standard(s)

UL Listed

Logistics

Carton Quantity

2

Product Assets

[Catalogs - WDK Catalog Full 2024](#)

[Literature - Wire Management Solutions Brochure](#)

[Specifications - 7401035](#)

[Warranty - Industrial & Commercial Products](#)