

# Kellems Wire Management, Deluxe Cord Grips, 90 Degree Male, .375-.500", 3/4" with Mesh

By Hubbell Wiring Device-Kellems  
Catalog # [07401081](#)



Kellems Wire Management, Deluxe Cord Grips, 90 Degree Male, .375-.500", 3/4" with Mesh

## Application

- 90 Degree Male- Form 3

## Performance

- Environmental - Flammability - UL 94HB (Strand grip), UL 94V-2(Fitting)
- Environmental - Hazardous Locations - Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C
- Environmental - Operating Temperatures - -30°F to +240°F (-34°C to +115°C)
- Environmental - Wet Locations - Suitable for use in wet locations when used with a listed sealing ring between box and fitting

## General

|                                     |  |
|-------------------------------------|--|
| Catalog Number                      | 07401081   |
| EU RoHS Indicator                   | Yes  |
| Environmental Conditions            | Suitable For Use In Wet Locations When Used With A Listed Sealing Ring Between Box And Fitting.  |
| Item Type                           | Deluxe Cord Grips  |
| Material                            | Aluminum Fittings, Stainless Steel Mesh  |
| Material - Mounting Hardware Series | Locknut or Tapped Opening Deluxe Cord Grips  |
| Specifications                      | <ul style="list-style-type: none"><li>Body - Aluminum</li><li>Bushing - Neoprene</li><li>Nut - Aluminum</li><li>Strand - Stainless Steel</li></ul> |

|                    |   |
|--------------------|---|
| Style              | For Insulated Cables                                    |
| Temperature Rating | Minimum -30 Deg F to 240 Deg F (-34 Deg C to 115 Deg C) |
| Thread Size        | 3/4" NPT  |
| Type               | 90 Degree Male Thread                                   |
| UPC                | 783585322629  |

## Dimensions

|              |          |
|--------------|----------|
| Display Size | 3/4" NPT |
|--------------|----------|

## Conductor Related

|                      |                            |
|----------------------|----------------------------|
| Cable Diameter Range | 0.375 in-0.500 in          |
| Cable Size           | .375"-.500" (.95-1.27)     |
| Conductor Range      | 0.375-0.5 in (.95-1.27 mm) |
| Number of Conductors | Single                     |

## Certifications And Compliance

|                                    |           |
|------------------------------------|-----------|
| Industry Standard(s)               | UL Listed |
| Standards - RoHS Compliance Status | CM        |

## Logistics

|                 |      |
|-----------------|------|
| Carton Quantity | 5    |
| Pallet Quantity | 1500 |

## Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Specifications - 7401081](#)
- [Warranty - Industrial & Commercial Products](#)