

Kellems Wire Management, Deluxe Cord Grips, 90 Degree Male, .375-.500", 3/4" with Mesh

By Hubbell Wiring Device-Kellems
Catalog # [07401081](#)



Kellems Wire Management, Deluxe Cord Grips, 90 Degree Male, .375-.500", 3/4" with Mesh

Application

- 90 Degree Male- Form 3

Performance

- Environmental - Flammability - UL 94HB (Strand grip), UL 94V-2(Fitting)
- Environmental - Hazardous Locations - Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C
- Environmental - Operating Temperatures - -30°F to +240°F (-34°C to +115°C)
- Environmental - Wet Locations - Suitable for use in wet locations when used with a listed sealing ring between box and fitting

General

Catalog Number	07401081
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Sealing Ring Between Box And Fitting.
Item Type	Deluxe Cord Grips
Material	Aluminum Fittings, Stainless Steel Mesh
Material - Mounting Hardware Series	Locknut or Tapped Opening Deluxe Cord Grips
Specifications	<ul style="list-style-type: none">Body - AluminumBushing - NeopreneNut - AluminumStrand - Stainless Steel

Style	For Insulated Cables
Temperature Rating	Minimum -30 Deg F to 240 Deg F (-34 Deg C to 115 Deg C)
Thread Size	3/4" NPT
Type	90 Degree Male Thread
UPC	783585322629

Dimensions

Display Size	3/4" NPT
--------------	----------

Conductor Related

Cable Diameter Range	0.375 in-0.500 in
Cable Size	.375"-.500" (.95-1.27)
Conductor Range	0.375-0.5 in (.95-1.27 mm)
Number of Conductors	Single

Certifications And Compliance

Industry Standard(s)	UL Listed
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	5
Pallet Quantity	1500

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Specifications - 7401081](#)
- [Warranty - Industrial & Commercial Products](#)