

## Kellems Wire Management, Deluxe Cord Grips, 90 Degree Male, .625-.750", 3/4" with Mesh

By Hubbell Wiring Device-Kellems  
Catalog # [07401084](#)



Kellems Wire Management, Deluxe Cord Grips, 90 Degree Male, .625-.750", 3/4" with Mesh

### Application

90 Degree Male- Form 3

### Performance

- Environmental - Flammability - UL 94HB (Strand grip), UL 94V-2(Fitting)
- Environmental - Hazardous Locations - Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C
- Environmental - Operating Temperatures - -30°F to +240°F (-34°C to +115°C)
- Environmental - Wet Locations - Suitable for use in wet locations when used with a listed sealing ring between box and fitting

### General

Catalog Number	07401084
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Sealing Ring Between Box And Fitting.
Item Type	Deluxe Cord Grips
Material	Aluminum Fittings, Stainless Steel Mesh
Material - Mounting Hardware Series	Locknut or Tapped Opening Deluxe Cord Grips
Specifications	<ul style="list-style-type: none"><li>Body - Aluminum</li><li>Bushing - Neoprene</li><li>Nut - Aluminum</li><li>Strand - Stainless Steel</li></ul>

Style	For Insulated Cables
Temperature Rating	Minimum -30 Deg F to 240 Deg F (-34 Deg C to 115 Deg C)
Thread Size	3/4" NPT
Type	90 Degree Male Thread
UPC	783585322650

### Dimensions

Display Size	3/4" NPT
--------------	----------

### Conductor Related

Cable Diameter Range	0.625 in-0.750 in
Cable Size	.625"-.750" (1.59-1.90)
Conductor Range	0.625-0.75 in (1.59-1.90 mm)
Number of Conductors	Single

### Certifications And Compliance

Industry Standard(s)	UL Listed
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	10
Pallet Quantity	1500

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Literature - Wire Management Solutions Brochure](#)  
[Sales Drawings - WDK\\_07401084\\_DRAWING\\_PDF](#)  
[Specifications - 7401084](#)  
[Warranty - Industrial & Commercial Products](#)