

# Kellems Wire Management, Deluxe Cord Grips, 90 Degree Male, .625-.750", 1" with Mesh

By Hubbell Wiring Device-Kellems  
Catalog # [07401087](#)

Kellems Wire Management, Deluxe Cord Grips, 90 Degree Male, .625-.750", 1" with Mesh



## Application

- 90 Degree Male- Form 4

## Performance

- Environmental - Flammability - UL 94HB (Strand grip), UL 94V-2(Fitting)
- Environmental - Hazardous Locations - Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C
- Environmental - Operating Temperatures - -30°F to +240°F (-34°C to +115°C)
- Environmental - Wet Locations - Suitable for use in wet locations when used with a listed sealing ring between box and fitting

## General

Catalog Number	07401087
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Sealing Ring Between Box And Fitting.
Item Type	Deluxe Cord Grips
Material	Aluminum Fittings, Stainless Steel Mesh
Material - Mounting Hardware Series	Locknut or Tapped Opening Deluxe Cord Grips
Specifications	<ul style="list-style-type: none"><li>• Body - Aluminum</li><li>• Bushing - Neoprene</li><li>• Nut - Aluminum</li></ul>

Style  
Temperature Rating  
  
Thread Size  
Type  
UPC

• Strand - Stainless Steel  
For Insulated Cables  
Minimum -30 Deg F to 240 Deg F (-34 Deg C to 115 Deg C)  
1" NPT  
90 Degree Male Thread  
783585322681

## Dimensions

Display Size 1" NPT

## Conductor Related

Cable Diameter Range 0.625 in-0.750 in  
Cable Size .625"-.750" (1.59-1.90)  
Conductor Range 0.625-0.75 in (1.59-1.90 mm)  
Number of Conductors Single

## Certifications And Compliance

Industry Standard(s) UL Listed  
Standards - RoHS Compliance CM  
Status

## Logistics

Carton Quantity 5

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Literature - Wire Management Solutions Brochure](#)  
[Specifications - 7401087](#)  
[Warranty - Industrial & Commercial Products](#)