

## Kellems Wire Management, Deluxe Cord Grips, Straight Male, 1.812-1.937", 2.5" with Mesh

By Hubbell Wiring Device-Kellems  
Catalog # [074011031](#)

Kellems Wire Management, Deluxe Cord Grips, Straight Male, 1.812-1.937", 2.5" with Mesh

### Application

- Straight Male- Form 7

### Performance

- Environmental - Flammability - UL 94HB (Strand grip), UL 94V-2(Fitting)
- Environmental - Hazardous Locations - Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C
- Environmental - Operating Temperatures - -30°F to +240°F (-34°C to +115°C)
- Environmental - Wet Locations - Suitable for use in wet locations when used with a listed sealing ring between box and fitting

### General

Catalog Number	074011031
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Sealing Ring Between Box And Fitting.
Item Type	Deluxe Cord Grips
Material	Aluminum Fittings, Stainless Steel Mesh
Material - Mounting Hardware Series	Locknut or Tapped Opening Deluxe Cord Grips
Specifications	<ul style="list-style-type: none"><li>• Body - Aluminum</li><li>• Bushing - Neoprene</li></ul>



Style	Nut - Aluminum
Temperature Rating	Strand - Stainless Steel For Insulated Cables Minimum -30 Deg F to 240 Deg F (-34 Deg C to 115 Deg C)
Thread Size	2 1/2" NPT
Type	Straight Male Thread
UPC	783585322858

### Dimensions

Display Size	2 1/2" NPT
--------------	------------

### Conductor Related

Cable Diameter Range	1.812 in-1.937 in
Cable Size	1.812"-1.937" (4.60-4.92)
Conductor Range	1.812-1.937 in (4.60-4.92 mm)
Number of Conductors	Single

### Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

### Logistics

Carton Quantity	12
-----------------	----

### Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Specifications - 74011031](#)
- [Warranty - Industrial & Commercial Products](#)