HUBBELL Wiring Device-Kellems

Kellems Wire Management, Deluxe Cord Grips, Straight Male, .625-.750", 1/2" with Mesh

By Hubbell Wiring Device-Kellems Catalog # 074011247

Kellems Wire Management, Deluxe Cord Grips, Straight Male, .625-.750", 1/2" with Mesh

Application

• Straight Male- Form 3

Performance

- Environmental Flammability UL 94HB (Strand grip), UL 94V-2(Fitting)
- Environmental Hazardous Locations Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C
- Environmental Operating Temperatures -30°F to +240°F (-34°C to +115°C)
- Environmental Wet Locations Suitable for use in wet locations when used with a listed sealing ring between box and fitting

General

Catalog Number 074011247 EU RoHS Indicator Yes

Environmental Conditions Suitable For Use In Wet

Locations When Used With A Listed Sealing Ring Between

Box And Fitting.

Deluxe Cord Grips

Item TypeDeluxe Cord GripsMaterialAluminum Fittings, Stainless

Steel Mesh

Material - Mounting Hardware

Series

Specifications

Locknut or Tapped Opening

Deluxe Cord GripsBody - Aluminum

• Bushing - Neoprene

Nut - Aluminum

• Strand - Stainless Steel

Style For Insulated Cables

Temperature Rating Minimum -30 Deg F to 240 Deg

F (-34 Deg C to 115 Deg C)

Thread Size 1/2" NPT

Type Straight Male Thread UPC 783585330303

Dimensions

Display Size 1/2" NPT

Conductor Related

Cable Diameter Range 0.625 in-0.750 in
Cable Size .625"-.750" (1.59-1.90)
Conductor Range 0.625-0.75 in (1.59-1.90 mm)

Number of Conductors Single

Certifications And Compliance

Industry Standard(s) UL Listed
Standards - RoHS Compliance CM

Status

Logistics

Carton Quantity 10
Pallet Quantity 3000

Product Assets

Catalogs - WDK Catalog Full 2024

Literature - Wire Management Solutions Brochure

Specifications - 74011247

Warranty - Industrial & Commercial Products

