

# Kellems Wire Management, Deluxe Cord Grips, Straight Male, 1.312-1.437", 2" with Mesh

By Hubbell Wiring Device-Kellems  
Catalog # [074011259](#)

Kellems Wire Management, Deluxe Cord Grips, Straight Male, 1.312-1.437", 2" with Mesh



## Application

- Straight Male- Form 6

## Performance

- Environmental - Flammability - UL 94HB (Strand grip), UL 94V-2(Fitting)
- Environmental - Hazardous Locations - Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C
- Environmental - Operating Temperatures - -30°F to +240°F (-34°C to +115°C)
- Environmental - Wet Locations - Suitable for use in wet locations when used with a listed sealing ring between box and fitting

## General

Catalog Number	074011259
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Sealing Ring Between Box And Fitting.
Item Type	Deluxe Cord Grips
Material	Aluminum Fittings, Stainless Steel Mesh
Material - Mounting Hardware Series	Locknut or Tapped Opening Deluxe Cord Grips
Specifications	<ul style="list-style-type: none"><li>• Body - Aluminum</li><li>• Bushing - Neoprene</li></ul>

## Style

Temperature Rating

## Thread Size

Type

UPC

## Dimensions

Display Size

## Conductor Related

Cable Diameter Range

Cable Size

Conductor Range

Number of Conductors

- Nut - Aluminum

- Strand - Stainless Steel

For Insulated Cables

Minimum -30 Deg F to 240 Deg

F (-34 Deg C to 115 Deg C)

2" NPT

Straight Male Thread

783585341354

2" NPT

1.312 in-1.437 in

1.312"-1.437" (3.33-3.65)

1.312-1.437 in (3.33-3.65 mm)

Single

## Certifications And Compliance

Industry Standard(s)

UL Listed

## Logistics

Carton Quantity

2

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)

[Literature - Wire Management Solutions Brochure](#)

[Specifications - 74011259](#)

[Warranty - Industrial & Commercial Products](#)