

Kellems Wire Management, Deluxe Cord Grips, Straight Male, Non-Metallic, .375-.500", 1/2" with Mesh

By Hubbell Wiring Device-Kellems
Catalog # [074011333](#)

Kellems Wire Management, Deluxe Cord Grips, Straight Male, Non-Metallic, .375-.500", 1/2" with Mesh



Application

Straight Male- Form 2

Performance

- Environmental - Flammability - UL 94HB (Strand grip), UL 94V-2(Fitting)
- Environmental - Hazardous Locations - Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C
- Environmental - Operating Temperatures - -40°F to +225°F (-40°C to +107°C)
- Environmental - Wet Locations - Suitable for use in wet locations when used with a listed sealing ring between box and fitting

General

Catalog Number	074011333
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Sealing Ring Between Box And Fitting.
Item Type	Deluxe Cord Grips
Material	Nylon Fittings, Stainless Steel Mesh
Material - Mounting Hardware Series	Locknut or Tapped Opening Deluxe Cord Grips
Specifications	<ul style="list-style-type: none">• Body - Nylon• Bushing - Neoprene• Nut - Nylon

Style	• Strand - Stainless Steel For Insulated Cables
Temperature Rating	Minimum -40 Deg F to 225 Deg F (-40 Deg C to 107 Deg C)
Thread Size	1/2" NPT
Type	Straight Male Thread
UPC	783585331041

Dimensions

Display Size	1/2" NPT
--------------	----------

Conductor Related

Cable Diameter Range	0.375 in-0.500 in
Cable Size	.375"-.500" (.95-1.27)
Conductor Range	0.375-0.5 in (.95-1.27 mm)
Number of Conductors	Single

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	5
Pallet Quantity	2200

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Specifications - 74011333](#)
- [Warranty - Industrial & Commercial Products](#)