

Kellems Wire Management, Deluxe Cord Grips, Straight Male, Non-Metallic, .875-1.000", 1" with Mesh

By Hubbell Wiring Device-Kellems
Catalog # [074011343](#)



Kellems Wire Management, Deluxe Cord Grips, Straight Male, Non-Metallic, .875-1.000", 1" with Mesh

Performance

- Environmental - Flammability - UL 94HB (Strand grip), UL 94V-2(Fitting)
- Environmental - Hazardous Locations - Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C
- Environmental - Operating Temperatures - -40°F to +225°F (-40°C to +107°C)
- Environmental - Wet Locations - Suitable for use in wet locations when used with a listed sealing ring between box and fitting

General

Catalog Number	074011343
Cord Range	.875"-1.000" (2.22-2.54)
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Sealing Ring Between Box And Fitting.
Item Type	Deluxe Cord Grips
Material	Nylon Fittings, Stainless Steel Mesh
Material - Mounting Hardware Series	Locknut or Tapped Opening Deluxe Cord Grips
Specifications	<ul style="list-style-type: none">• Body - Nylon• Bushing - Neoprene• Nut - Nylon• Strand - Stainless Steel
Style	For Insulated Cables
Temperature Rating	Minimum -40 Deg F to 225 Deg F (-40 Deg C to 107 Deg C)

Thread Size	1" NPT
Type	Straight Male Thread
UPC	783585331140

Dimensions

Dimensions	1.88 in x 1.88 in x 2.45 in
Display Size	1" NPT
Height	2.45 in
Length	1.88 in
Weight	0.15 lb
Width	1.88 in

Conductor Related

Cable Diameter Range	0.875 in-1.000 in
Cable Size	.875"-1.000" (2.22-2.54)
Conductor Range	.875"-1.000" (2.22-2.54)
Number of Conductors	Single

Certifications And Compliance

Industry Standard(s)	UL Listed
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - Wire Management Solutions Brochure](#)
[Specifications - 74011343](#)
[Warranty - Industrial & Commercial Products](#)