

# Kellems Wire Management, Deluxe Cord Grips, Straight Metric Male, M20 Thread

By Hubbell Wiring Device-Kellems  
Catalog # [074M20010](#)

Kellems Wire Management, Deluxe Cord Grips, Straight Metric Male, M20 Thread



## Application

- Straight Male- Form 2

## Performance

- Environmental - Flammability - UL 94HB (Strand grip), UL 94V-2 (Fitting)
- Environmental - Hazardous Locations - Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C
- Environmental - Operating Temperatures - -30°F to +240°F (-34°C to +115°C)
- Environmental - Wet Locations - Suitable for use in wet locations when used with a listed sealing ring between box and fitting

## General

Catalog Number	074M20010
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Sealing Ring Between Box And Fitting.
Item Type	Deluxe Cord Grips
Material	Aluminum Fittings, Stainless Steel Mesh
Material - Mounting Hardware Series	Locknut or Tapped Opening PG and Metric Threaded
Specifications	<ul style="list-style-type: none"><li>• Body - Naluminum</li><li>• Bushing - Neoprene</li><li>• Nut - Aluminum</li></ul>

Style	• Strand - Stainless Steel For Insulated Cables
Temperature Rating	Minimum -30 Deg F to 240 Deg F (-34 Deg C to 115 Deg C)
Type	Straight Metric Male Thread
UPC	783585327686

## Dimensions

Display Size	20mm
Hub Size	M20

## Conductor Related

Cable Diameter Range	0.500 in-0.625 in
Cable Size	.500"-.625" (1.27-1.59)
Conductor Range	0.5-0.625 in (1.27-1.59 mm)
Number of Conductors	Single

## Certifications And Compliance

Industry Standard(s)	UL Listed
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	5
-----------------	---

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Literature - Wire Management Solutions Brochure](#)  
[Specifications - 074M20010](#)  
[Warranty - Industrial & Commercial Products](#)