

Kellems Wire Management, Deluxe Cord Grips, Straight Metric Male, M32 Thread

By Hubbell Wiring Device-Kellems
Catalog # [074M32021](#)

Kellems Wire Management, Deluxe Cord Grips, Straight Metric Male, M32 Thread



Application

Straight Male- Form 4

Performance

- Environmental - Flammability - UL 94HB (Strand grip), UL 94V-2 (Fitting)
- Environmental - Hazardous Locations - Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C
- Environmental - Operating Temperatures - -30°F to +240°F (-34°C to +115°C)
- Environmental - Wet Locations - Suitable for use in wet locations when used with a listed sealing ring between box and fitting

General

Catalog Number	074M32021
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Sealing Ring Between Box And Fitting.
Item Type	Deluxe Cord Grips
Material	Aluminum Fittings, Stainless Steel Mesh
Material - Mounting Hardware Series	Locknut or Tapped Opening PG and Metric Threaded
Specifications	<ul style="list-style-type: none">• Body - Aluminum• Bushings - Neoprene• Nut - Aluminum

Style
Temperature Rating

- Strand - Stainless Steel For Insulated Cables
- Minimum -30 Deg F to 240 Deg F (-34 Deg C to 115 Deg C)
Straight Metric Male Thread
783585327730

Type
UPC

Dimensions

Display Size 32mm
Hub Size M32

Conductor Related

Cable Diameter Range 0.625 in-0.750 in
Cable Size .625"-.750" (1.59-1.90)
Conductor Range 0.625-0.75 in (1.59-1.90 mm)
Number of Conductors Single

Certifications And Compliance

Industry Standard(s) UL Listed
Standards - RoHS Compliance CM
Status

Logistics

Carton Quantity 5

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - Wire Management Solutions Brochure](#)
[Specifications - 074M32021](#)
[Warranty - Industrial & Commercial Products](#)