

## Kellems Wire Management, Deluxe Cord Grips, Straight Male, .500-.625", PG21 with Mesh

By Hubbell Wiring Device-Kellems  
Catalog # [074PG21010](#)

Kellems Wire Management, Deluxe Cord Grips, Straight Male,.500-.625", PG21 with Mesh



### Application

- Straight Male- Form 2

### Performance

- Environmental - Flammability - UL 94HB (Strand grip), UL 94V-2 (Fitting)
- Environmental - Hazardous Locations - Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C
- Environmental - Operating Temperatures - -30°F to +240°F (-34°C to +115°C)
- Environmental - Wet Locations - Suitable for use in wet locations when used with a listed sealing ring between box and fitting

### General

Catalog Number	074PG21010
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Sealing Ring Between Box And Fitting.
Item Type	Deluxe Cord Grips
Material	Aluminum Fittings, Stainless Steel Mesh
Material - Mounting Hardware Series	Locknut or Tapped Opening PG and Metric Threaded
Specifications	<ul style="list-style-type: none"><li>• Body - Aluminum</li><li>• Bushing - Neoprene</li></ul>

Style

Temperature Rating

Type

UPC

### Dimensions

Display Size

Hub Size

- Nut - Aluminum
  - Strand - Galvanized Steel
- For Insulated Cables  
Minimum -30 Deg F to 240 Deg F (-34 Deg C to 115 Deg C)  
Straight PG Male Thread  
783585327754

PG21

PG21

### Conductor Related

Cable Diameter Range

Cable Size

Conductor Range

Number of Conductors

0.500 in-0.625 in

.500"-.625" (1.27-1.59)

0.5-0.625 in (1.27-1.59 mm)

Single

### Certifications And Compliance

Industry Standard(s)

### Logistics

Carton Quantity

UL Listed

5

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)

[Literature - Wire Management Solutions Brochure](#)

[Specifications - 074PG21010](#)

[Warranty - Industrial & Commercial Products](#)