

Kellems Wire Management, Deluxe Cord Grips, Straight Male, .625-.750", PG21 with Mesh

By Hubbell Wiring Device-Kellems
Catalog # [074PG211247](#)

Kellems Wire Management, Deluxe Cord Grips, Straight Male,.625-.750", PG21 with Mesh



Application

- Straight Male- Form 3

Performance

- Environmental - Flammability - UL 94HB (Strand grip), UL 94V-2 (Fitting)
- Environmental - Hazardous Locations - Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C
- Environmental - Operating Temperatures - -30°F to +240°F (-34°C to +115°C)
- Environmental - Wet Locations - Suitable for use in wet locations when used with a listed sealing ring between box and fitting

General

Catalog Number	074PG211247
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Sealing Ring Between Box And Fitting.
Item Type	Deluxe Cord Grips
Material	Aluminum Fittings, Stainless Steel Mesh
Material - Mounting Hardware Series	Locknut or Tapped Opening PG and Metric Threaded
Specifications	<ul style="list-style-type: none">• Body - Aluminum• Bushing - Neoprene

Style

Temperature Rating

Type

UPC

Dimensions

Display Size

Hub Size

- Nut - Aluminum

• Strand - Galvanized Steel
For Insulated Cables

Minimum -30 Deg F to 240 Deg F (-34 Deg C to 115 Deg C)

Straight PG Male Thread

783585327846

PG21

PG21

Conductor Related

Cable Diameter Range

Cable Size

Conductor Range

Number of Conductors

0.625 in-0.750 in

.625"-.750" (1.59-1.90)

0.625-0.75 in (1.59-1.90 mm)

Single

Certifications And Compliance

Industry Standard(s)

Logistics

Carton Quantity

UL Listed

5

Product Assets

[Catalogs - WDK Catalog Full 2024](#)

[Literature - Wire Management Solutions Brochure](#)

[Specifications - 074PG211247](#)

[Warranty - Industrial & Commercial Products](#)