



# Switches and Lighting Controls, Hubbell- PRO Series, Toggle Switches, General Purpose AC, Three Way, 15A 120/277V AC, Back and Side Wired, Ivory

By Hubbell Wiring Device-Kellems  
Catalog # [12031](#)



Switches and Lighting Controls, Hubbell- PRO Series, Toggle  
Switches, General Purpose AC, Three Way, 15A 120/277V AC,  
Back and Side Wired , Ivory

## Features

- Steel, zinc plated bridge is corrosion resistant
- Color Coded by Amperage makes inspection easy even when installed
- Strip gauge for accurate wiring

## Application

Back and Side Wired

## General

Action	SPDT
Color	<ul style="list-style-type: none"> <li>• Ivory</li> <li>• Ivory</li> </ul>
Number Of Poles	Single Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> <li>• Electrical - Dielectric Voltage - Withstands 1500V AC minimum for 1 minute</li> <li>• Electrical - Max. Continuous Current - 15A</li> <li>• Electrical - Max. Working Voltage - 277V AC</li> <li>• Electrical - Overload - Minimum 4.8 times rated current for 100 cycles</li> <li>• Electrical - Temperature Rise - 30°C maximum at rated current</li> <li>• Environmental - Flammability - UL 94V-2</li> <li>• Environmental - Operating Temperature - Max. continuous: 75°C, Min. continuous: -40°C without impact</li> <li>• Mechanical - Terminal Accommodations - #14 AWG min. - #10 AWG max.</li> </ul>

## Dimensions

Dimensions	4.18 in x 1.49 in x 1.83 in
Height	1.83 in
Length	4.18 in
Weight	0.15 lb
Width	1.49 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 1500V AC minimum for 1 minute
Temperature Rise - Max.	30°C maximum at rated current
Voltage Rating	120-277 VAC
Voltage Rating Description	120-277 VAC

## Conductor Related

Wire Size	#14 AWG to #10 AWG
-----------	--------------------

## Certifications and Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalogs - WDK Catalog Full 2023](#)  
[Warranty - Industrial & Commercial Products](#)

solid and stranded copper  
wire only

Series	Heavy Duty
Style	Three Way
Type	<ul style="list-style-type: none"><li>• Toggle</li><li>• Toggle</li></ul>
UPC	783585835204



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_MX-1203I-SPEC-EN | REV 1/2024