

Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, 2- Pole 3-Wire Grounding, 20A 125V, 5-20R, Ivory

By Hubbell Wiring Device-Kellems
Catalog # 5362I



Straight Blade Devices, Receptacles, Duplex,
Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A
125V, 5-20R, Ivory

Application

Hubbell-Pro Extra Heavy Duty

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V-2
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #12-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminal wire leads identified in accordance with UL 498

General

Catalog Number	5362I
Color	Ivory
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry unless protected by additional means
Horsepower - Maximum	1
Item Type	Traditional Duplex
Material	Thermoplastic/Composite
Material - Mounting Hardware	Screw Mounting
Mounting Type	Screw Mount
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Hubbell-PRO
Size	Standard Sized Product
Specifications	<ul style="list-style-type: none">• Automatic Self-grounding Staple - Stainless steel• Base - PBT• Contacts - Brass• Face - Nylon

Style

Temperature Rating

Type

UPC

Dimensions

Dimensions	3.28 in x 1.41 in x 1.09 in
Display Size	Standard Sized Product
Height	1.09 in
Length	3.28 in
Weight	0.2 lb
Width	1.41 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	UL File No. E2186, Certified to CSA 22.2, No. 42 File 285, Fed.
----------------------	---

- Mounting Screws - Zinc plated steel
 - Mounting Strap - Galvanized steel
- Finder Groove Face
Maximum continuous 75°C;
minimum -40°C (w/o impact)
Standard Duplex
783585835006

Nema Rating
Standards - RoHS Compliance
Status

Spec. W-C-596, NEMA® WD-6
Compliant
5-20R
CM

Carton Quantity 10
Pallet Quantity 4500

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - 5362I](#)
[Warranty - Industrial & Commercial Products](#)

Logistics



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-5362I-SPEC-EN | REV 10/2024