

Kellems Wire Management, Liquidtight System, PolyTuff® II Non-Metallic Tubing, 1/4", 100 feet, Black

By Hubbell Wiring Device-Kellems
Catalog # [B2025](#)



Kellems Wire Management, Liquidtight System, PolyTuff® II Non-Metallic Tubing, 1/4", 100 feet, Black

General

Application	UL1660
Catalog Number	B2025
Color	Black
EU RoHS Indicator	Yes
Finish Type	Ribbed
Item Type	Standard Product
Load Capacity	Extra Flexible
Material	Co-extruded rigid and flexible PVC
Performance	Electrical - Voltage Rating - 300V Maximum Environmental - Operating Temperature - 0°F to +140°F (-18°C to +60°C)
Type	PolyTuff® II Liquidtight Tubing PolyTuff® II Liquidtight Tubing
UPC	783585333151

Dimensions

Length	100 ft
Trade Size	1/4
Width	0.57 in

Electrical Ratings

Voltage Rating	300 V
----------------	-------

Certifications And Compliance

Industry Standard(s)	CSA Certified UL Recognized
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	100
-----------------	-----

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Customer Notices - Prop 65 Notice](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Literature - Safety Product Guide](#)
- [Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-B2025-SPEC-EN | REV 6/2024