

# Kellems Wire Management, Liquidtight System, PolyTuff® II Non-Metallic Tubing, 3/8", 100 feet, Black

By Hubbell Wiring Device-Kellems  
Catalog # B2038



Kellems Wire Management, Liquidtight System, PolyTuff® II Non-Metallic Tubing, 3/8", 100 feet, Black

## Application

- UL1660

## Performance

- Electrical - Voltage Rating - 300V Maximum
- Environmental - Operating Temperature - 0°F to +140°F (-18°C to +60°C)

## General

Catalog Number	B2038
Color	Black
EU RoHS Indicator	Yes
Finish Type	Ribbed
Item Type	Standard Product
Load Capacity	Extra Flexible
Material	Co-extruded rigid and flexible PVC
Specifications	<ul style="list-style-type: none"><li>• Bend Radius Inches (mm) - 2.00" (50.8)</li><li>• Conduit ID/OD Inches (mm) - .49"/.70" (12.6/17.8)</li><li>• Material - Co-extruded rigid and flexible PVC</li><li>• Trade Size - 3/8 Inch</li></ul>
Type	PolyTuff® II Liquidtight Tubing

UPC 783585333168

## Dimensions

Length 100 ft  
Trade Size 3/8  
Width 0.7 in

## Electrical Ratings

Voltage Rating 300 V

## Certifications And Compliance

Industry Standard(s) 

- CSA Certified
- UL Recognized

  
Standards - RoHS Compliance CM  
Status

## Logistics

Carton Quantity 100

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Literature - Wire Management Solutions Brochure](#)  
[Literature - Safety Product Guide](#)  
[Specifications - B2038](#)  
[Warranty - Industrial & Commercial Products](#)