

Kellems Wire Management, Liquidtight System, PolyTuff® II Non-Metallic Tubing, 3/4", 100 feet, Black

By Hubbell Wiring Device-Kellems
Catalog # [B2075](#)



Kellems Wire Management, Liquidtight System, PolyTuff® II Non-Metallic Tubing, 3/4", 100 feet, Black

Application

- UL1660

Performance

- Electrical - Voltage Rating - 300V Maximum
- Environmental - Operating Temperature - 0°F to +140°F (-18°C to +60°C)

General

Catalog Number	B2075
Color	Black
EU RoHS Indicator	Yes
Finish Type	Ribbed
Item Type	Standard Product
Load Capacity	Extra Flexible
Material	Co-extruded rigid and flexible PVC
Specifications	<ul style="list-style-type: none">• Bend Radius Inches (mm) - 3.00" (76.2)• Conduit ID/OD Inches (mm) - .83"/1.04" (21.1/26.4)• Material - Co-extruded rigid and flexible PVC• Trade Size - 3/4 Inch
Type	PolyTuff® II Liquidtight Tubing
UPC	783585333229

Dimensions

Length	100 ft
Trade Size	3/4
Width	1.04 in

Electrical Ratings

Voltage Rating	300 V
----------------	-------

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified• UL Recognized
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	100
Pallet Quantity	2000

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Literature - Safety Product Guide](#)
- [Specifications - B2075](#)
- [Warranty - Industrial & Commercial Products](#)