



# Kellems Wire Management, Liquidtight System, PolyTuff® II Non-Metallic Tubing, 1", 100 feet, Black

By Hubbell Wiring Device-Kellems  
Catalog # [B2100](#)



Kellems Wire Management, Liquidtight System, PolyTuff® II  
Non-Metallic Tubing, 1", 100 feet, Black

## Application

UL1660

## General

Color	<ul style="list-style-type: none"><li>• Black</li><li>• Noir</li></ul>
Finish Type	Ribbed
Item Type	Standard Product
Load Capacity	Extra Flexible
Material	Co-extruded rigid and flexible PVC
Performance	<ul style="list-style-type: none"><li>• Electrical - Voltage Rating - 300V Maximum</li><li>• Environmental - Operating Temperature - 0°F to +140°F (-18°C to +60°C)</li></ul>
Type	<ul style="list-style-type: none"><li>• PolyTuff® II Liquidtight Tubing</li><li>• PolyTuff® II Liquidtight Tubing</li></ul>
UPC	78358533243

## Dimensions

Length	100 ft
Trade Size	1
Width	1.30 in

## Electrical Ratings

Voltage Rating	300 V
----------------	-------

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• CSA Certified</li><li>• UL Recognized</li></ul>
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	100
Pallet Quantity	2000

## Product Assets

[Catalogs - WDK Catalog Full 2023](#)  
[Literature - Wire Management Solutions Brochure](#)  
[Literature - Safety Product Guide](#)  
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_MX-B2100-SPEC-EN | REV 1/2024