



Kellems Wire Management, Liquidtight System, PolyTuff® II Non-Metallic Tubing, 1 1/4", 100 feet, Black

By Hubbell Wiring Device-Kellems
Catalog # [B2125](#)



Kellems Wire Management, Liquidtight System, PolyTuff® II
Non-Metallic Tubing, 1 1/4", 100 feet, Black

Application

UL1660

General

Color	<ul style="list-style-type: none"> • Black • Noir
Finish Type	Ribbed
Item Type	Standard Product
Load Capacity	Extra Flexible
Material	Co-extruded rigid and flexible PVC
Performance	<ul style="list-style-type: none"> • Electrical - Voltage Rating - 300V Maximum • Environmental - Operating Temperature - 0°F to +140°F (-18°C to +60°C)
Type	<ul style="list-style-type: none"> • PolyTuff® II Liquidtight Tubing • PolyTuff® II Liquidtight Tubing
UPC	78358533274

Dimensions

Length	100 ft
Trade Size	1 1/4
Width	1.65 in

Electrical Ratings

Voltage Rating	300 V
----------------	-------

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified • UL Recognized
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	100
Pallet Quantity	600

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Literature - Wire Management Solutions Brochure](#)
[Literature - Safety Product Guide](#)
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_MX-B2125-SPEC-EN | REV 1/2024