

Kellems Wire Management, Liquidtight System, PolyTuff® II Non-Metallic Tubing, 1 1/2", 50 feet, Black

By Hubbell Wiring Device-Kellems
Catalog # B2150



Kellems Wire Management, Liquidtight System, PolyTuff® II Non-Metallic Tubing, 1 1/2", 50 feet, Black

Application

UL1660

Performance

- Electrical - Voltage Rating - 300V Maximum
- Environmental - Operating Temperature - 0°F to +140°F (-18°C to +60°C)

General

Catalog Number	B2150
Color	Black
EU RoHS Indicator	Yes
Finish Type	Ribbed
Item Type	Standard Product
Load Capacity	Extra Flexible
Material	Co-extruded rigid and flexible PVC
Specifications	<ul style="list-style-type: none">• Bend Radius Inches (mm) - 5.00" (127.0)• Conduit ID/OD Inches (mm) - 1.59"/1.88" (40.3/47.8)• Material - Co-extruded rigid and flexible PVC• Trade Size - 1 1/2 Inch
Type	PolyTuff® II Liquidtight Tubing
UPC	783585333298

Dimensions

Length	50 ft
Trade Size	1 1/2
Width	1.88 in

Electrical Ratings

Voltage Rating	300 V
----------------	-------

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified• UL Recognized
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	50
Pallet Quantity	500

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Literature - Safety Product Guide](#)
- [Specifications - B2150](#)
- [Warranty - Industrial & Commercial Products](#)