

Kellems Wire Management, Liquidtight System, PolyTuff® II Non-Metallic Tubing, 2", 50 feet, Black

By Hubbell Wiring Device-Kellems
Catalog # [B2200](#)



Kellems Wire Management, Liquidtight System, PolyTuff® II Non-Metallic Tubing, 2", 50 feet, Black

Application

- UL1660

Performance

- Electrical - Voltage Rating - 300V Maximum
- Environmental - Operating Temperature - 0°F to +140°F (-18°C to +60°C)

General

Catalog Number	B2200
Color	Black
EU RoHS Indicator	Yes
Finish Type	Ribbed
Item Type	3A
Load Capacity	Extra Flexible
Material	Co-extruded rigid and flexible PVC
Specifications	<ul style="list-style-type: none">• Bend Radius Inches (mm) - 5.00" (127.0)• Conduit ID/OD Inches (mm) - 2.03"/2.36" (51.6/59.9)• Material - Co-extruded rigid and flexible PVC• Trade Size - 2 Inch
Type	PolyTuff® II Liquidtight Tubing
UPC	783585333311

Dimensions

Length	50 ft
Trade Size	2
Width	2.36 in

Electrical Ratings

Voltage Rating	300 V
----------------	-------

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified• UL Recognized
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	1
Pallet Quantity	350

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Literature - Safety Product Guide](#)
- [Product Cross Section Image\(s\) - BUR_BCS-8_LineArt](#)
- [Specifications - B2200](#)
- [Warranty - Industrial & Commercial Products](#)