

2-Gang, Rectangular, Galvanized Stamped Steel Box, Shallow, Fully Adjustable, Brass Top

By Hubbell Wiring Device-Kellems
Catalog # [B2422](#)



Flush Concrete Floor Box Series, 2-Gang, Rectangular,
Galvanized Stamped Steel Box, Shallow, Fully Adjustable, Brass
Top

Application

Multi Service In-Floor Delivery Systems

General

| | |
|--------------------------|--|
| Application - For Use On | Concrete |
| Catalog Number | B2422 |
| Color | Brass Flange |
| Construction | Fabricated |
| EU RoHS Indicator | No |
| Knockouts | 6)1/2", 4) 3/4", 4)3/4"-1 1/4" |
| Material | Galvanized Stamped Steel |
| Mounting Method | Cast Into Concrete |
| Number of Gang(s) | 2-Gang |
| Series | Flush Rectangular - B24 Series |
| Size | 2-Gang |
| Specifications | <ul style="list-style-type: none">• Collar Material - Brass• Cubic Capacity - 35.0 cu. in. (573.5 cm³)• Min. Depth of Pour - 2.75" (69.9)• Size - 2-Gang |

Type

2-Gang Shallow Rectangular
Galvanized Stamped Steel Box
783585100258

UPC

Dimensions

| | |
|------------|-----------------------------|
| Dimensions | 4.81 in x 9.25 in x 2.74 in |
| Height | 2.74 in |
| Length | 4.81 in |
| Width | 9.25 in |

Conductor Related

Cable Entry From Top

Certifications And Compliance

| | |
|----------------------|--|
| Industry Standard(s) | <ul style="list-style-type: none">• UL/CSA• UL514 |
|----------------------|--|

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Customer Notices - Prop 65 Notice](#)
[Specifications - B2422](#)
[Warranty - Industrial & Commercial Products](#)