

2-Gang, Rectangular Cast Iron Box, Deep, Fully Adjustable, Brass Top

By Hubbell Wiring Device-Kellems
Catalog # [B423341](#)



Flush Concrete Floor Box Series, 2-Gang, Rectangular Cast Iron Box, Deep, Fully Adjustable, Brass Top

Application

- Multi Service In-Floor Delivery Systems

General

Application - For Use On	Concrete
Catalog Number	B423341
Color	Brass Flange
Construction	Case Iron
EU RoHS Indicator	No
Finish Type	Brass
Knockouts	6)1" and 2) 3/4"
Material	Cast Iron
Mounting Method	Cast Into Concrete
Number of Gang(s)	2-Gang
Series	Flush Rectangular - B24 Series
Size	3-Gang
Specifications	<ul style="list-style-type: none">Capacity Per Gang - 36.5 cu. in. (598.1 cm³)Collar Material - BrassMin. Depth of Pour - 3.75" (95.3)

Type	2-Gang Deep Rectangular Cast Iron Box
UPC	783585102801

Dimensions

Dimensions	4.84 in x 8.06 in x 3.38 in
Height	3.38 in
Length	4.84 in
Width	8.06 in

Conductor Related

Cable Entry	From Top
-------------	----------

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">UL/CSAUL514
----------------------	--

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Customer Notices - Prop 65 Notice](#)
[Specifications - B423341](#)
[Warranty - Industrial & Commercial Products](#)