

2-Gang, Rectangular, Galvanized Stamped Steel Box, Shallow, Fully Adjustable, Aluminum Top

By Hubbell Wiring Device-Kellems
Catalog # [BA2422](#)



Flush Concrete Floor Box Series, 2-Gang, Rectangular,
Galvanized Stamped Steel Box, Shallow, Fully Adjustable,
Aluminum Top

Application

- Multi Service In-Floor Delivery Systems

General

Application - For Use On	Concrete
Catalog Number	BA2422
Color	Aluminum Flange
Construction	Fabricated
EU RoHS Indicator	No
Knockouts	4)1/2", 2) 3/4", 2) 3/4"- 1 1/4 in Combo
Material	Galvanized Stamped Steel
Mounting Method	Cast Into Concrete
Number of Gang(s)	2-Gang
Series	Flush Rectangular - B24 Series
Size	2-Gang
Specifications	<ul style="list-style-type: none">• Collar Material - Aluminum• Cubic Capacity - 35.0 cu. in. (573.5 cm³)• Min. Depth of Pour - 2.75" (69.9)• Size - 2-Gang

Type

2-Gang Shallow Rectangular
Galvanized Stamped Steel Box
783585104256

UPC

Dimensions

Dimensions	4.81 in x 9.25 in x 2.74 in
Height	2.74 in
Length	4.81 in
Width	9.25 in

Conductor Related

Cable Entry From Top

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• UL/CSA• UL514
----------------------	--

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - BA2422](#)
[Warranty - Industrial & Commercial Products](#)