

# Straight Blade Devices, Receptacles, Tamper-Resistant Duplex, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Single Pack

By Hubbell Wiring Device-Kellems  
Catalog # [BR15WHITR](#)



Straight Blade Devices, Receptacles, Tamper-Resistant Duplex,  
Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A  
125V, 5-15R, White, Single Pack.

## Application

- Commercial Specification Grade

## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V-2
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

## General

Catalog Number	BR15WHITR
Color	White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Item Type	Traditional Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Commercial Specification Grade
Specifications	<ul style="list-style-type: none"> <li>• Automatic Self-grounding Staple - Stainless steel</li> <li>• Base - Nylon</li> <li>• Face - Nylon</li> <li>• Ground Contacts - Brass</li> </ul>

- Mounting Screws - Galvanized Steel
- Mounting Strap - .040 in. (1) Galvanized steel
- Power Contacts - .030 in. (.8) Brass
- Terminal Screws - Plated steel
- Wire Clamp - .062 in. (1.6) Nickel plated steel

Style  
Type  
UPC

Smooth Face  
Tamper-Resistant  
783585144092

## Dimensions

Dimensions	1.32 in x 0.83 in x 3.28 in
Display Size	Standard Sized Product
Height	3.28 in
Length	1.32 in
Weight	0.15 lb
Width	0.83 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

## Certifications And Compliance

Industry Standard(s)

- Certified to CSA C22.2, No. 42
- NEMA® WD-6 Compliant
- UL Listed to UL498 File No. E2186

Nema Rating 5-15R  
Standards - RoHS Compliance CM  
Status

### Logistics

Carton Quantity 10  
Pallet Quantity 8000

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs](#)  
[Specifications - BR15WHITR](#)  
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-BR15WHITR-SPEC-EN | REV 10/2024