



Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, 2- Pole 3-Wire Grounding, 20A 125V, 5-20R, Ivory, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [BR20I](#)



Straight Blade Devices, Receptacles, Duplex,
Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A
125V, 5-20R, Ivory, Single Pack.

Features

- Easy access split circuit tab
- Nylon face and base
- Wrap-around galvanized steel strap
- Triple wipe contacts

Application

Commercial Specification Grade

General

Color	<ul style="list-style-type: none"> • Ivory • Ivoire
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	1
Item Type	Traditional Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - UL 94 V-2 • Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact) • Mechanical - Product Identification - Ratings are a permanent part of the device • Mechanical - Terminal Accommodation - #12-#10

Dimensions

Dimensions	1.32 in x 0.83 in x 3.28 in
Display Size	Standard Sized Product
Height	3.28 in
Length	1.32 in
Weight	0.55 lb
Width	0.83 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #10 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA 22.2, No. 42 • Fed. Spec. W-C-596 • NEMA® WD-6 Compliant • UL Listed to UL498 File No. E2186
----------------------	--

Nema Rating	5-20R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Customer Notices - Prop 65 Notice](#)

AWG copper stranded or solid conductor only

- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

Series	Commercial Specification Grade
Style	Smooth Face
Type	<ul style="list-style-type: none">• Standard Duplex• Standard Duplex
UPC	783585834887



A proud member of the Hubbell Family.